

ELECTRONIC THEODOLITE

RUIDE produces 2 main serieses of electronic theodolites. ET Series, which has been put into production for years and has mature technology, employs the Incremental Photoelectronic Encoding measurement method. For DT Series that has a simplified structure and credible capability, it employs the Absolute Encoding measurement method, which enables it free of Manual Initialization (ie. it can work without rotating the lens.) and restores the previous measured data even after reboot.





ET-02/05

Series

Internal memory system for 256 pairs of H.&V. angle

ET/DT -02/05 Series



1___

1

Accessories





AA Battery Case / Rechargeable Battery





Diagonal Eyepiece

Specifications

	ET-02/ET-02L	ET-05/ET-05L
TELESCOPE		
Image	Erect	
Magnification	30×	
Effective aperture	45mm	
Resolving power	3 ″	
Field of view	1° 30′	
Min. focuse distance	1.4m	
Stadia ratio	100	
Stadia constant	0	
Tube length	157mm	
ANGLE MEASUREMENT		
Method	Absolute Encoding	
Diameter of circle(VHz)	79mm	
Minimum reading	1" / 5" / 10" /20" (Selectable)	
accuracy	2 "	5 ″
Horizontal angle Vertical angle	Dual Dual	Dual Single
DISPLAY		
Screen type	2 sides, segment LCD in two lines	
DATA OUTPUT		
DATA I/ O	RS-232C	
LEVEL SENSITIVITY	<i>"</i>	
Plate level	30 ″ / 2mm	
Circular level	8′ / 2mm	
AUTO VERTICAL COMPENSATOR		
System	Liquid-electric detection/ Plate Level	
Compensating Range	±3′	
Accuracy	1 (Liquid-electric detection)30" /2mm(Plate level)	
OPTICAL PLUMMET TELES	COPE	
Image	3×	
Magnification	.5∧ 0.5m~∞	
Focusing range	0.5m~00	
Field of view	-	
PHYSICAL CHARACTERIST		FT-021/051 : YES
Laser pointer Temperature range	ET-02/05: NO	
Internal power supply	−20°C ~ +45°C Ni-MH / AA battery	
Voltage	ET: 6VDC DT:5VDC	
Operating time	ET: 6VDC DT:5VDC	
Dimension	10 hours	
Weight		
Weight	4.3kg	

RUIDE